

Waukesha Model 125 Positive Displacement Pump

Mfg: Waukesha

Model: 125 U1

Stock No: OIP148.

Serial No: D055263

Waukesha Positive Displacement Pump. Model: 125 U1. S/N: D055263. Flow rate for new pump is 140 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum Speed: 590 rpm. Reliance Electric motor, 7 ½ hp, 1755 rpm, 230/460 V, 21/10.5 amps, 60 Hz, 3 phase. Reeves drive, ratio: 6.2:1, rpm out: 283 (final). Waukesha sanitary pumps feature easy cleaning and disassembly. The 125's non-galling '88' alloy rotors provide minimum breakage on fluids with delicate particles such as diced tomatoes. Typical products handled by Waukesha U1-series pumps include products from bakery, beverage, canning, confectionary, cosmetics, dairy, meat packaging, and pharmaceutical industries. Inlets/outlets: (2) 2 ½ in. dia. ACME fittings. Overall dimensions: 4 ft. 2 in. L x 1 ft. 7 in. W x 2 ft. 7 in. H.(ACN116).



