

## Waukesha Model 220 Positive Displacement Pump

Mfg: Waukesha

Model: 220

Stock No: SNCC092.33

Serial No: 134527

Waukesha Positive Displacement Pump. Model 220. SN: 134527. Flow rate for new pump is 310 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum allowable speed: 600 rpm. Baldor motor, 15 Hp. 1765 rpm. 460 Volts. 60 Hz. 3 phase. Baldor motor, 1/3 hp. 3450 rpm. 115/208-230 Volts. 2.5/1.3-1.25 Amps. 60 Hz. 3 phase. Sew-Eurodrive speed reducer. Ratio 13.01:1. Final rpm: 135. Seal option: double mechanic seal with water flush. Inlet: (1) 4 in. dia. (male). Outlet: (1) 4 in. dia. (male). Overall dimensions: 6 ft. 11 in. L x 1 ft. 6-1/2 in. W x 2 ft. 7 in. H.(ACN226).





