

APV Crepaco Plate Heat Exchanger with Titanium and Stainless Steel Plates - 478 sq. ft.

Mfg: APV Crepaco

Model: R405-S

Stock No.: 35.184

Serial No.: 18279

APV Crepaco Plate Heat Exchanger. Model: R405-S. S/N 18279. Total amount of plates: 85 (14 are titanium and 71 are 316 stainless steel.) Plate dimensions: 3ft. 9-1/4 in. L x 1ft. 5-1/2 in. W. Heat transfer area: approx. 478 sq. ft. Inlets: (2) 4 in. ID dia. product inlet, (2) 4 in. ID dia. steam inlet. Outlets: (2) 4 in. ID dia. product, (2) 4 in. ID dia. steam, all with 8 bolt flange connections. The APV R405-S is ideal for most marine applications or where sea water is used as a cooling water for long periods of time. Overall dimensions: 5 ft. 1 in. L x 2 ft.10 in. W x 5 ft. 3 in. H.



