

Copeland Discus 6-Cylinder Semi-Hermetic Compressor – 40 HP

Mfg: Copeland

Model: 6DS3-4000-TSN-800

Stock No.: 20.6

Serial No.: 98J77466

Copeland Discus 6-Cylinder Semi-Hermetic Compressor – 40 HP. Model: 6DS3-4000-TSN-800. S/N: 98J77466. Displacement: 90 cfm. Capacity: 39 tons of R-22 at a 45°F suction temperature, 130°F condensing temperature, and a 65°F return gas temperature. Power supply: 230/460 V, RLA: 142/71, LRA: 594/297, 60 Hz, 3 phase. Inlet: (1) 2-1/2 in. dia. suction port. Outlet: (1) 1-1/4 in. dia. discharge port. Overall dimensions: 2 ft. 6 in. L x 1 ft. 10 in. W x 1 ft. 11 in. H.(ACN60).

