

607 Gallon Tolan Processor

607 Gallon Tolan Processor, split lift covers, stainless, agitator motor
1 - 1/2 HP 220/440V 1800/900 RPM 50/25 Final RPM, less jacket
rating, 2 in outlet, (2) 1 - 1/2 in jacket inlets with hand valves and
(3) 1 - 1/2 in outlets, 3 in top inlet on bridge, 3 blade propeller with 26 in spread

inner dimensions 66 in Dia x 41 in H,
overall dimensions 71 in Dia x 73 in H



3/2/2004





