

Trane 6-Cylinder Reciprocating Compressor - 50 Tons

Mfg: Trane

Model: CRHR5004HAT

Stock No: 80.RB259C.

Serial No: 466033-755

Trane 6-Cylinder Reciprocating Compressor . Model: CRHR5004HAT. S/N: 466033-755. Rated at 50 tons for R-22. Displacement in CFM: 129.9. Power supply: 460 V, 396 LRA, 60 Hz, 3 phase. Unloads at 115V. Unloads at 115V. Inlets: (1) 1-1/4 in. dia. copper tube (refrigerant suction port). Outlets: (1) 2 in. dia. copper tube (refrigerant discharge port). Overall dimensions: 3 ft. 6 in. L x 2 ft. 1 in. W x 2 ft. 2 in. H.(ACN164).



