1990 Bertoli High Pressure Pump	
Mfg: Bertoli	Model: PQ120N
Stock No.: 85.CA60a.5	Serial No.: 573PQ120N

1990 Bertoli High Pressure Pump. Model: PQ120N. S/N: 573PQ120N. Maximum capacity: 1716 gph. 2 in. dia. plungers. Tapered seat poppet valve cylinders. Maximum pressure 1740 psi (120 Bar). ABB Motor, 60 hp (45 kW), 1770 rpm, 460 V, 71 amps, 60 Hz, 3 phase. High Pressure Pump is equipped with a hydraulic power pack as well as oil filters and blower fan. Hydraulic Pump with Motor, 1/2 hp (0.37 kW), 1410 rpm, 220/380 V, 1.95/1.1 amps, 50 Hz, 3 phase. Inlets/outlets: (2) 2 in. dia. S-line fittings. Overall dimensions: 6 ft. 3 in. L x 4 ft. 8 in. W x 61 in. H.











































