

Tri Clover PRE 300 Positive Displacement Pump

Mfg: Tri Clover

Model: PRE300-4M-VC4-SL-S

Stock No: AAC4764.27

Serial No: V9813

Tri Clover PRE 300 Positive Displacement Pump. Model: PRE300-4M-VC4-SL-S. S/N: V9813. Ports: 4 in. Tri-clamp fittings. Flow rate for a new pump is 300 gpm at max rpm of 500. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Pump has mechanical seals. Drive can be changed to suit your application. Reliance motor: 10 hp, 1755 rpm, 230/460 V, 27.0/13.5 amps, 60 Hz, 3 phase. Viking Helical Gear Reducer: 7.95 ratio, 220 rpm output, part number: 3-551-012-795, size C. Overall dimensions: 4 ft. 10 in. L x 1 ft. 6 in. W x 2 ft. H.







