

Waukesha Cherry Burrell Votators on Stainless Steel Frame

Mfg: Waukesha Cherry Burrell

Model: 6 x 72

Stock No: AANF346.45

Serial No:

(3) Waukesha Cherry Burrell Votators on Stainless Steel Frame. Model: 6 x 72. (3) Sew-Eurodrive, Inc Gearmotor RX series. Motor: 7.5 hp, 1720 rpm, 230/460V, 60 Hz, 3 phase. Gear unit: Ratio 3.87, Output: 444 final rpm. Product tubes: 6 in inside diameter, 72 in length. Product ports: 2 in. I-line fittings. Shell MAWP: 400 PSI at 375°F and Shell MDMT: -20°F at 400 PSI. Jacket MAWP: 80 PSI at 375°F and Jacket MDMT: -20°F at 80 PSI. Jacket ports: 1 ½ in. FNPT fittings. Mutator shaft is mounted using concentric design. Discuss with salesperson your process and product to determine if these votators should handle your specific duty. Mutator are currently Celcon material. Blades and drives can be changed to suit you application. Overall dimensions: 11 ft. 7 in. L x 5 ft. 1 in. W x 6 ft. 1 in. H.









