

Ohio Geared Head and Westinghouse Motor

Mfg:

Model:

Stock No: AANF400

Serial No:

Ohio Geared Head and Westinghouse Motor. 240 V, 7.5 HP, 3 PH, 1750/2300 RPM, continuous duty.



Westinghouse STANDARD		Life-Line S	
DIRECT CURRENT MOTOR			
HP	7.5	RPM	1750/2300
ARM VOLTS	240	ARM AMPS	27.2
WOUND	SPLIT	ENCLOSURE	355
SER. FACTOR	1.0	INSULATION	CL. F
FRAME	256-A	POWER SUPPLY	TYPE C DR D
BRUSH STYLE	769A7B4G03	TEMPERATURE	130°C
SHUNT FIELD	100	AMPS	
CONNECTED LINE	197.7	VOLTS	300
PARALLEL CONNECTED LINE	49.4	VOLTS	150
STYLE	2644B40G08	SERIAL	355
WESTINGHOUSE ELECTRIC CORPORATION 199P167401A MADE IN U.S.A.			