

Waukesha 30 Positive Displacement Pump

Mfg: SPX Waukesha Cherry Burrell

Model: 030

Stock No.: AAWI01.

Serial No.: 79730 SS

Waukesha Positive Displacement Pump. Model: 030. Serial: 79730 SS. A3 certified design. Displacement per revolution: 0.060 gallons (0.227 liters). Nominal capacity: 36 GPM (8.2 m3/hr). Maximum pressure: 200 PSI (13.8 bar). Speed range: 0-600 RPM. Temperature range: -40F to 300 F (-40C to 149C). Reeves Variable Speed Gear Drive: 6.2 ratio, 84-420 final RPM. Baldor motor: 3 HP, 230/460V, 8.2 / 4.12 amps, 1725 RPM, MAS-51 gear drive. Weight: 130 lbs (pump only). Port size: 1.5 in. tri-clamp. (ACN57a)



