

## 1999 Carrier Air Cooled Chiller - 100 Tons

Mfg: Carrier

Model: 30GT100 610KA

Stock No: ABCC202.50

Serial No: 2999F35349


1999 Carrier Air Cooled Chiller. Model: 30GT100 610KA. Serial No: 2999F35349. Rated nominal cooling capacity: 100 tons. Refrigerant: R-22. Respective high and low design/test pressures: 450/278 psi. (4) Carlyle compressors. Model: 06EF275310: 208/230-460V, 60 Hz, 3 phase, or 400V, 50 Hz, 3 phase. (8) fans, 6 blades, 30 in. diameter, 1.0 hp, 460V, 60 Hz, 3 phase. Overall dimensions: 15 ft. 2 in. L x 8 ft. 2 in. W x 8 ft. 2 in. H.











**Carrier** 30GT-100---610KA  
2999F35349

MODEL 30GT-100---610KA		SERIAL 2999F35349		FACTORY CHARGED	
QTY	VOLTS AC	PH HZ	RLA	LRA	NET WT. LB
COMP 2	460	3 60	43.6	223	98 LBS 11.5 kg
COMP 2	460	3 60	46.8	253	105 LBS 17.7 kg
COMP					
DESIGN / TEST PRESSURE GAGE		HIGH PSI 450	kPa 3103	LOW PSI 278	kPa 1917
FAN MOTORS QTY	VOLTS AC	PH HZ	FLA	HP	kW OUT
OUTDOOR 6	460	3 60	3.3	1	.746
OUTDOOR 2	460	3 60	2.8	1	.746
OTHER					
HEATERS TOTAL ONLY SUITABLE FOR OUTDOOR USE					
POWER SUPPLY	460 VOLTS	3 PH	60 HZ	MIN CIRCUIT AMPS	MAX OVERCURRENT PROTECTION (50% AMPS)
PERMISSIBLE VOLTAGE AT UNIT	506 MAX	414 MIN		217.9	250 FUSE OR HICR-TYPE CIRCUIT BREAKER
CONTROL POWER SUPPLY	115 VOLTS	1 PH	60 HZ	30 AMPS	2

MADE IN U.S.A. CHARGE SYSTEM PER INSTALLATION INSTRUCTIONS 99NA504514

57R9 LISTED



