

## Viking M-Series Rotary Positive Displacement Pump

Mfg: Viking

Model: M4125

Stock No.: ACEU2011

Serial No.: 2538898

Viking M-Series Rotary Positive Displacement Pump. Model: M4125. S/N: 2538898. Nominal Capacity: 400 gpm @ 25 psi. Reliance Electric Motor, 20 hp, 1755 rpm, 230/460 V, 46/23 amps, 60 Hz, 3 phase. Inlets: (1) 4 in. dia. flanged suction port. Outlets: (1) 4 in. dia. flanged discharge port. Overall dimensions: 6 ft. 9 in. L x 2 ft. W x 2 ft. 1 in. H. (ACN83a)







