

## Grundfos / Paco Pumps Centrifugal Pump


**Mfg: Grundfos / Paco Pumps**

**Model: 40955**

**Stock No: ACEU77bb**

**Serial No: KRB47091A**

Grundfos / Paco Pumps Centrifugal Pump. Model: 40955. S/N:KRB47091A. Flow rate for new pump is 1200 gpm with required horsepower and pressure. Impeller diameter: 9-1/2 in. Energy Efficient electric motor: 15 hp, 1770 rpm, 208-230/460 V, 41-38/19.4 amps, 60 Hz, 3 phase. Inlet: (1) 5 in. dia. flanged port. Outlet: (1) 4 in. dia. flanged port. Overall dimensions: 4 ft. L x 1 ft. 7 in. W x 1 ft. 7 in. H.



MODEL NO.	3K46B		FR	2541	
FD	INSUL CLASS	F	MAX AMB	30	°C DUTY
BRG	6309-2Z-J/03			OPP END BRG	63
	LOT AESSA 01067231 006 F				US 20
HP	15	RPM	1770		HP
VOLTS	208-230/460			VOLTS	190/
FL AMPS	41.0-38.8/19.4			FL AMPS	46.8
SF AMPS	44.2/22.1			SF AMPS	-
SF	1.15	DESIGN	8	CODE	5
NEMA NOM EFFICIENCY	91.0	NOM PF	79.5		NEMA NOM EFFICIENCY
GUARANTEED EFFICIENCY	89.5	MAX KVAR	5.9		GUARANTEED EFFICIENCY

**Energy Efficient Indu**

11409557462011822

KRB47091A

490 75