

## York Air Cooled Liquid Chiller- 25 Ton

Mfg: York

Model: LCHA25-46E

Stock No. ACEU9151.20

Serial No. GM-423108

York Air Cooled Liquid Chiller- 25 Ton. Model: LCHA25-46E. S/N: GM-423108. Power supply: 460 V, 73 min. ckt. ampacity, 100 amps max., 60 Hz, 3 phase. York/Borg Warner 6-Cylinder Reciprocating Compressor, Model: SS6213-J46G, S/N: LM11463211, date code: 1072403, refrigerant: R-22, test pressure (hi/lo): 450/330 psig, 460/380 V, 225/216 LRA, 60/50 Hz, 3 phase. York Chiller Barrel, S/N: 5242, shell side MAWP: 150 psi @ 150 °F, shell side MDMT: -20 °F @ 150 psi, tube side MAWP: 225 psi @ 150 °F, tube side MDMT: -20 °F @ 150 psi. (4) 24 in. Fan Motors, 3/4 hp, 208/230 V, 4.5 FLA, 12.4 LRA, 60 Hz, single phase. Controls power supply: 115 V, 15 amps, 60 Hz. Inlets/outlets: (2) 3 in. dia. flanged ports. Overall measurements: 10 ft. 9 in. L x 74 in. W x 50 in. H.



