

York Chiller-25 Ton Model LCHA25-46E

Mfg: York

Model: LCHA25-46E

Stock No. ACEU9152a.20

Serial No. KM047926

York Chiller-25 Ton. Model LCHA25-46E. S/N KM047926. 460 V, 3 phase, 60 Hz. Minimum circuit ampacity 73, 100 amps, max fuse size 72. Compressor: 460 V, 3 phase, 60 Hz, FLA51, LRA 225. (4) fan motors: 3/4 hp, 208/230 V, 1 phase, 60 Hz, FLA 4.5, LRA 12.4. Voltage limits of terminals 414 min, 506 max. 115 V supply, 60 hz, 15A. Inlet: 3-1/2 in.; outlet: 3-1/2 in. Overall dimensions: 129 in. L x 74 in. W x 49 in. H.





