

Vilter VMC-326 6-Cylinder Reciprocating Compressor

Mfg: Vilter

Model: VMC-326

Stock No: ANTZ001.5

Serial No: R2082

Vilter VMC-326 6-Cylinder Reciprocating Compressor. Model: VMC-326. S/N: R2082. Size: MK326. Order No: H-69718. Refrigerant: Freon use only. Last used with R-22. Nominal capacity: 79 tons at 77 bhp with a 105 °F condensing temperature and a 40 °F suction temperature. Displacement: 171 cfm @ 1800 rpm. Maximum discharge pressure: 300 psi. Maximum discharge temperature: 300 °F, Hydrostatic test pressure: 600 psi high side; 375 psi low side, 115 V require for oil heaters. Inlet: (1) 3-5/8 in. dia. suction port. Outlet: (1) 2-5/8 in. dia. discharge port. Approximate compressor weight: 1,500 lbs. Overall dimensions: 3 ft. 5 in. L x 2 ft. 8 in. W x 2 ft. 3 in. H.



REFRIGERATION AIR CONDITIONING	VILTER TM		HEAT EXCHANGE PH: (414) 744-0111
CUDAHY, WISCONSIN 53110		REFRIGERANT	R-22
SERIAL NO.	R2082	COMPRESSOR FRAME HYDROSTATIC TEST (PSIG)	
ORDER NO.	H-69718	HIGH SIDE	LOW SIDE
SIZE	MK326	600	375
		VOLTAGE	115V