

APV Crepaco pump, Centrifugal Pump, Model 16V2, S/N H-0895-93, sitting on a stainless steel frame with 2 casters and control panel. Reliance Electric Motor, S/N P14H4506N-RT, 208/230/460 volt, 3 phase, 60 Hz, 5.8-5.6 2.8 amp, 2.0 hp, 3,450 rpm. (1) 3 in. inlet, (1) 2in. outlet. Overall dimensions 20 in. L x 37 in. W x 38 in. H.

