

APV Crepaco pump, Model 16V2, S/N H-3579-93 , sitting on stainless steel base with 2 wheels and a stainless steel control panel. Reliance Electric Motor, S/N P14H4506P-RU, 208/230/460 volt, 3 phase, 60 Hz, 5.8-5.6 2.8 amp, 2.0 hp, 3450 rpm. (1) 3 in. inlet, (1) 2in. outlet Overall dimensions 20 in. L x 37 in. W x 38 in. H.

