

## RVS Medium Temp Recirculator 72 in Dia x 13 ft H

**Mfg: RVS**

**Model:**

**Stock No: ASCA025.17a**

**Serial No: 91378**

RVS Recirculator Package. 6 ft. dia. x 13 ft. H. Nat. bd: 3813. S/N: 91378. Year built: 1991. MAWP 150 psi at 300°F. Minimum design metal temp -20°F at 150 psi. (2) Teikoku Stainless Steel Canned Motor Pumps. Type: R42-526C4M-1012V1-E. Inlet: 5 in. Outlet: 4 in. Header: 6 in. Head 157 ft. Capacity: 274 gal./min. 14.7 HP, 60 HZ, 460 V, 15 kW, 32 A. Product no: FZ-1323-1 & FZ-1323-2. Manufactured March 2007.

