

## Elima-Matic Diaphragm Pump 2 in.

Mfg: Versa-Matic


Model: Elima-Matic E2

Stock No. BAFB95.5

Serial No. R005252

### Versa-Matic Polypropylene Diaphragm Pump.

- Model Elima-Matic E2,
- S/N R005252.
- Date of Mfg: 4/19/02.
- 2 in. Inlet, 2 in. outlet,
- W/TX/TF/TES & center port MNF,
- Adjustable flowrate 0-155 gpm.
- Overall Dimensions 12 in. W x 17 in. L x 29 in. H.



# E2 2" Plastic Bolted Pumps: Optional Porting Specifications and Performance

## SPECIFICATIONS

E2

**FLOW RATE** (Adjustable) .... 0-155 gpm (586 lpm)  
**PORT SIZE**

Inlet and Outlet..... 2.0" ANSI, 150 Class (DIN 50)

**AIR INLET** ..... 0.50" NPT

**AIR EXHAUST** ..... 0.75" NPT

**SUCTION LIFT** .... 20' Dry/25' Wet (6.10m/7.62m)

Teflon®..... 10' Dry/20' Wet (3.05m/6.10m)

**MAX. PARTICLE SIZE** (Dia.) ..... 0.25"(6.35mm)

### SHIPPING WEIGHTS

E2PA ..... 76.2 lbs (34.56 kg)

E2PS ..... 110.2 lbs (49.99 kg)


E2KA ..... 102.2 lbs (46.36 kg)

E2KS ..... 136.2 lbs (61.78 kg)



## PERFORMANCE Determined by actual flow meter tests.

E2



**NOTE:** For E2P pumps fitted with Teflon® diaphragms, reduce water discharge figures by 20%. Suction lift is reduced to 10' (3.05m) dry and 20' (6.10m) wet.

**CAUTION:** Do not exceed 100 psig (6.9 bars) air supply or liquid pressure.  
**Adjustable Inlet/Discharge.**

## DIMENSIONS Consult factory for certified drawings.

E2

