

Horizontal Ammonia Receiver - 475 Gallons

Mfg:

Model:

Stock No: BDNP09

Serial No:

Horizontal Ammonia Receiver. Approximate capacity: 475 gallons. Straight wall dimensions: 30 in. dia. x 12 ft. 5 in. L. (14) valves to include: (12) Vilter and Hansen LCB series hand shut-off valves and (2) Hansen Technologies Corp. pressure relief Valves. Serial no: 05B04. Cat. No: H5602, air capacity: 768 SCFM, set pressure: 250 PSI. Outlets: (4) at 1 in., (1) at 1-3/4 in., (1) at 2 in., and (1) 3-1/2 in. Overall dimensions: 14 ft. L x 3 ft. 9-1/2 in. W x 5 ft. 3-1/2 in. H.(H16).



