

Tri Clover Centrifugal Pump

Mfg: Tri Clover

Model: C114MD56T

Stock No. BFLV151B.

Serial No. 253629-01

Tri Clover Centrifugal Pump. Model: C114MD56T. S/N: 253629-01. Pump capacity: 57.5 gpm at 30 ft. Impeller: 3 in. diameter. The C Series features and benefits; hydraulically balanced seal reduces pressure at sealing, surface, that means less seal wear for longer life and less downtime, an easy-to-clean, open-type impeller delivers smoother pumping performance, pump takedown is fast and easy, no tools are required, casing is secured with a quick-opening clamp, impeller is secured via a retainer pin. Leeson Motor, 3 hp, 3450 rpm, 208-230/460 V, 8/4 amps, 60 Hz. Inlet/outlet: 1-1/2 in. $\frac{1}{2}$ sqline. Overall dimensions: 19 in. L x 9 in. W x 10 in. H.

