

1984 Cherry Burrell Processing Tank 2,000 Gallons

Mfg: Cherry Burrell

Model: EP

Stock No. BIIR402.

Serial No.

Cherry Burrell Processor Tank- 2,000 Gallon. Model: EP. S/N: 2000-84-2825. 304 stainless steel. Atmospheric tank with dome top. Tank is equipped with (5) zone control valves, (4) 2-1/2 in. dia. header connections, (1) 18 in. manway, (2) 3/4 in. dia. indicating/recording thermometer wells, (1) 2 in. dia. air space heater opening, (1) 2 in. air space thermometer opening, and (1) 2-1/2 in. dia. flush type outlet valve. Processor heating/cooling recommended operating range is 45 psig and below; maximum operating range for the Deluxe Header is 75 psig. Tank comes equipped with wide bottom side sweep agitator, baffle, and dual spray balls. Reliance Electric Motor- 3/1.5 hp, 1735/865 rpm, 230/230 V, 8.4/6.2 amps, 60/60 Hz, 3 phase. Reliance Electric Master XL Motor Drive- 101.0 ratio, 17 rpm (out). Overall dimensions: 112 in. L x 101 in. W x 142-3/8 in. H.





