

Vilter 6-Cylinder Reciprocating Compressor

Mfg: Vilter

Model: VMC 446

Stock No.: BIIR7002

Serial No.: 13762ARC

Vilter 6-Cylinder Reciprocating Compressor. Model: VMC 446. S/N: 13762ARC. Order No: C734323. Refrigerant: ammonia. Displacement at maximum rpm: 232 cu. ft./min. Electrical requirements: 115 V. Inlets: (1) 4 in. dia. refrigerant suction port. Outlets: (1) 3 in. dia. refrigerant discharge port. Overall dimensions: 44 in. L x 39 in. W x 32 in. H.





