

Vilter 6-Cylinder Reciprocating Compressor

Mfg: Vilter

Model: VMC 446

Stock No. B1IR7004.

Serial No. _____

Vilter 6-Cylinder Reciprocating Compressor. Model: VMC 446. Refrigerant: Ammonia. Displacement at maximum rpm: 232 cu. ft./min. Pulley diameter: 17 in. Inlets: (1) 4 in. dia. refrigerant suction port. Outlets: (1) 3 in. dia. refrigerant discharge port. Overall dimensions: 3 ft. 8 in. L x 3 ft. 3 in. W x 2 ft. 8 in. H.

