

Tri Clover Positive Rotary Displacement Pump PRED Series

Mfg: Tri Clover


Model: PRED125-2-1/2-TC1-4-WT-S

Stock No. BIIR8005B.

Serial No. U2156

Tri Clover Positive Displacement Rotary Pump PRED Series. Model: PRED125-2-1/2-TC1-4-WT-S. S/N: U2156. Seal option: wet seals. Reliance Electric Motor, 7-1/2 hp, 1755 rpm, 230/460 V, 21/10.5 amps, 60 Hz, 3 phase. Nord Gear Drive, ratio: 7.90, torque: 4770 lb-in. rpm out: 222 (final). Inlets/outlets: 2 in. dia. ACME fittings. Overall dimensions: 4 ft. 8 in. L x 1 ft. 7 in. W x 1 ft. 5 in. H.





RELIANCE®			
FRAME	TYPE	DESIGN	IDE
213TC		B	21
HP 7.5	VOLTS	230/460	
RPM 1755	AMPS	21/10.5	
AMB 40	°C DUTY	CONT	
DRIVE END BEARING	35BC02JPF30A25		
OPP. D.E. BEARING	30BC02J-P30A25		

