

Sundyne Maso / Sine MR Series Positive Displacement Pump



Mfg: Sundyne Maso / Sine

Model: MR150-NNTC

Stock No. BIIR8005.

Serial No. _____

Sundyne Maso / Sine MR Series Positive Displacement Pump. Model: MR150-NNTC. Materials of construction: 316 stainless steel. Capacity: 100gpm, (0.47 gallons/revolution). Size: 4 x 4. Baldor Indus). trial Motor, 10 hp, 1725 rpm, 460 V, 13.5 amps, 60 Hz, 3 phase. Dodge APG Drive, ratio: 7.6, torque: 9587 lb-in. rpm out: 226 (final). Inlets/outlets: (2) 4 in. dia. S-line fittings. Approved for 3A applications, and meets USDA requirements for meat, poultry and dairy. MR pumps features include: Low shear rotors, low pulsation for constant volumetric displacement, powerful suction capabilities, and easy maintenance. Overall dimensions: 5 ft. 7in. L x 2 ft. 5 in. W x 2 ft. 2 in. H.



CHEMICAL

PROCESSING

CORROSION

PROTECTED

SPEC.	07H01W100		
FRAME	2151	ER.	F799
H.P.	10	1B	
VOLTS	460		
AMPS	13.5		
R.P.M.	1725		
HZ.	60	PH.	CLASS
SER. F.	71.15	DES.	CODE
RATING	400 AMB-CONT		
CAT. NO.	VCP377A1-9		
PULL LOAD EFF.	87.5%	P.F.	98.5%

BALDOR

FT. SMITH, ARK. U.S.A.



© 1977