

Sundyne Maso Sine MR Series Positive Displacement Pump

Mfg: Sundyne Maso Sine

Model: MR150-NNTC

Stock No. BIIR8017.

Serial No. 1000134-01

Sundyne Maso Sine MR Series Positive Displacement Pump. Model: MR150-NNTC. S/N: 1000134-01. Nominal Capacity: 282 gpm. Maximum speed: 600 rpm @ 150 psi. Reliance Electric Motor, 20 hp, 1760, 230/460 V, 47.0/23.5 amps, 60 Hz, 3 phase. Speed reducer. ratio: 4.1, 427 rpm out (final), torque: 5740 lb-in. Inlets/outlets: (2) 4 in. dia. S-line fittings. Design advantages include: powerful suction for viscous products, low pulsation for smooth, consistent flow, and low shear for fragile and shear-sensitive products. Typical applications include: cheese, curd & whey, cottage cheese, butter, yogurt, fruit concentrates, syrups and beers. Overall dimensions: 5 ft. 5 in. L x 2 ft. W x 1 ft. 11 in. H.



