

## Hansen Technologies AP08 Auto-Purger

**Mfg: Hansen Technologies**

**Model: AP08**

**Stock No.: BNCA160.2a**

**Serial No.: N2450**

Hansen Technologies AP08 Auto Purger. Model: AP08. S/N: N2450. Number of purge points: 8. Refrigerant: R-717 (ammonia). Maximum allowable working pressure: 400 psig. MDMT: -60°F. Power supply: 120 V, 3.0 amps, 60 Hz. Evaporator Chamber. Receiver - 1.5 Gallon, straight-wall dimensions: 5 in. dia. x 1 ft. 8 in. L. Hoffman Control Panel. The Auto-Purger features automatic startup with electronic controls, automatic water bubbler, relief valve, and an isolation service valve. This unit quickly and efficiently removes air from a refrigeration system which reduces the energy costs of operating an ammonia refrigeration system. Includes Inlets: (2) 1 in. dia. FNPT fitting. Outlets: (1) 1 in. dia. port, (2) 1 in. dia. FNPT fittings. Overall dimensions: 4 ft. 7 in. L x 3 ft. 1 in. W x 1 ft. 5 in. H.(ACN95a).





