

## Simplimatic Engineering Systems Belt Conveyor

<b>Mfg:</b>	<b>Model:</b>
<b>Stock No. BP19.</b>	<b>Serial No.</b>

Simplimatic Engineering Systems Belt Conveyor. Maximum aperture/clearance above belt: 10 in. W x 12-1/2 in. H. Available with 21 in. L x 15 in. W roller conveyor and attachment. (4) Limit switches for 250 and 400 ml. bottles. Sew Eurodrive Motor: 0.75 hp, 1,700 rpm, 230/460 V, 3.05/1.53 amps, 60 Hz, 3 phase. Sew Eurodrive Motor Drive: 16.25 ratio, 1,700 rpm (input), 105 rpm (output), 450 lb-in. torque. Overall dimensions: 11 ft. 10 in. L x 34-1/2 in. W x 40 in. H. Omron Sysmac C200H Control panel for Belt Conveyor. RAM with auxiliary battery: 16 Kb. Dimensions: 39 in. L x 12 in. W x 51 in. H.



