

Vilter VMC 440 Reciprocating Compressor, Size 446

Mfg: Vilter

Model: VMC 440

Stock No. BRDI802.20

Serial No. R15050

Vilter VMC 440 Reciprocating Compressor. S/N: R15050. Size: A10K446B. Cylinders: 6. Refrigerant: Freon or ammonia. Compressor frame hydrostatic test pressure high/low side: 525/375 psig. Compressor is available with a Frick Dyna Metric control box, 2-1/2 in. dia. x 17 in. L Vilter oil cooler, and 4 in. dia. x 8-1/2 in. L Vilter chiller barrel. Design pressure: 400 psig max @ -20 to 400 F. Baldor Industrial Motor: 75 hp, 1760 rpm, 200 V, 200 amps, 60 Hz, 3 phase. Inlets/outlets: (3) 3/4 in. dia. pipes, (1) 3 in. dia. pipe, (1) 4 in. dia. pipe. Overall dimensions: 82 in. L x 51 in. W x 46 in. H.

