

Vilter VMC 440 Reciprocating Compressor, Size 446

Mfg: Vilter

Model: VMC 440

Stock No. BRDI803.20

Serial No. 33256

Vilter VMC 440 Reciprocating Compressor. S/N: 33256. Size: MK446. Order No: F91894. Cylinders: 6. Refrigerant: Freon or ammonia. Compressor frame hydrostatic test pressure high/low side: 525/375 psig. Compressor is available with Frick Dyna Metric control box and 2-1/2 in. dia. x 17 in. L Vilter Oil Cooler. Design pressure: 300 psig @ 400 F. Shell side test pressure: water cooled, 100 psig. Tube side test pressure: refrigerant cooled, 375 psig. Gould Century Motor: 75 hp, 1770 rpm, 200-208 V, 200-192 amps, 3 phase. Inlets/outlets: (1) 1/2 in. dia. MPT, (2) 3/4 in. dia. MPT, (1) 4 in. dia. with 6 in. L x 6 in. W flange and (4) 3/4 in. dia. attachment holes at a center-to-center distance of 6 in., (1) 4 in. dia. with 7-1/2 in. L x 7-1/2 in. W flange and (4) 3/4 in. dia. attachment holes at a center-to-center distance of 7-1/2 in. Overall dimensions: 83 in. L x 47 in. W x 51 in. H.

