

Viking H224A Universal Seal Gear Pump

Mfg: Viking Pump, Inc. (IDEX Corp)

Model: H224A

Stock No.: CAGC1087

Serial No.: 11714567

Viking Gear Pump. Model H224A. Serial: 11714567. Nominal pump rating: 15 GPM at 1750 RPM. Max hydrostatic pressure: 400 PSIG, max discharge pressure 200 PSIG. Max temperature: 450F. Approx pump weight: 42 lbs (without motor/base). Ports: 1.5 in. SEW-Eurodrive ratio 4.35 (391 final RPM). Motor: 1 HP, 1700 RPM, 230/460V, 3-phase, 60 Hz, TEFC.





