

Groen Steam Jacketed Gas Kettle- 40 Gallon

Mfg: Groen

Model: AH/1-40

Stock No. CARA001.6

Serial No. _____

Groen Steam Jacketed Gas Kettle- 40 Gallon. Model: AH/1-40. Nat'l Bd: 77210. Gas-fired: natural. MAWP @ 300 °F: 30 psi. Input rate: 100,000 Btu/h. Open top with lift-top lid. Electrical requirements: 115 V, 1 amp, 60 Hz, single phase. Inlets: (1) 3/4 in. dia. FNPT (jacket), (1) 1/2 in. dia. MNPT (natural gas), (1) 2 in. dia. pilot access door. (1) 4 in. burner sight port. Outlets: (1) 1-1/2 in. dia. discharge, (1) 6 in. dia. exhaust port. Overall dimensions: 3 ft. 6 in. L x 3 ft. W x 3 ft. 9 in. H. (ACN97).



