

2005 – Caterpillar 10,000 Lb. 4x4x4 Diesel Telescopic Telehandler Forklift

Mfg: Caterpillar

Model: TH560B

Stock No: CBHT1619.500

Serial No: CRX06140 / MP405708

2005 Caterpillar 4x4x4 Telescopic Telehandler Forklift. Model: TH560B. S/N: CRX06140 / MP405708. Load capacity rating: 10,000 lb. Four section boom telescopes to total distance of 55 ft. Maximum lift height: 44 ft. 3 in. Maximum horizontal reach: 30 ft. 2-½ in. Capacity at Maximum reach: 4000 lb (with stabilizers.) Engine: 4 cylinder diesel. Tire Size : 14.00-24TG, Flywheel: 94.9 hp. This unit features: foam filled tires for added protection in hazardous conditions, safety canopy, tilting carriage, three steering modes for improved maneuverability, outriggers, auxiliary hydraulics and hydraulic leveling. Caterpillar telehandlers offer spacious cabs and suspension seats for added comfort. The single lever joystick contains all boom functions for easy operation. Overall dimensions (fully retracted): 26 ft. L x 8 ft. 7 in. W x 9 ft. 2 in. H. Hour meter reading: 2804 hrs.(ACN118a).









CAT CATERPILLAR
CAT CATERPILLAR

MODEL NUMBER TH560B

PRODUCT IDENTIFICATION NUMBER *CATTH560VSLG00911*

MODEL NUMBER	SERIAL NUMBER	ARRANGEMENT NUMBER
0	6N2051A1	1525000
0	M2477H	1525000

225-4150 3

CATERPILLAR INC.
PEORIA, IL 61629
USA
MADE IN PARTS OTHER

LK