

**2005 Caterpillar 9,000 Lb. 4x4x4 Diesel Telescopic Telehandler Forklift**

**Mfg: Caterpillar**

**Model: TH460B**

**Stock No: CBHT1637.330**

**Serial No: CRX08187 / EP507562**

2005 Caterpillar 4x4x4 Diesel Telescopic Telehandler Forklift. Model: TH460B. S/N: CRX08187 / EP507562. Load capacity rating: 9,000 lb. Three section boom telescopes to total distance of 46 ft. Maximum lift height: 44 ft. 3 in. Maximum horizontal reach: 30 ft. 2-½ in. Capacity at maximum reach: 1800 lbs. Engine: 4 cylinder diesel. Tire size: 14.00-24TG, Flywheel: 94.9 hp. This unit features: optional work lights, safety canopy, tilting carriage, three steering modes for improved maneuverability, auxiliary hydraulics and hydraulic leveling. Caterpillar telehandlers offer spacious cabs and suspension seats for added comfort. The single lever joystick contains all boom functions for easy operation. Overall dimensions (fully retracted): 26 ft. L x 8 ft. 7 in. W x 8 ft. 3 in. H. Hour meter reading: 2732 hrs.(ACN892).














03-30-2009: Antonio initial update. New pics + extended description. Kept all info. on currently on web tag.

<b>Click On Picture</b> 	<b>2005 - Caterpillar TH460B 9,000 Lb 4x4x4 Telescopic Forklift</b>	
	Mfg: <b>Caterpillar</b>	Model: <b>TH460B</b>
<b>Get A Quote</b>	Stock No: <b>CBHT1637.330</b>	Serial No: <b>CATTH460CSLF01796</b>
	2005 - Caterpillar TH460B 9,000 Lb 4x4x4 Telescopic Forklift. Model: TH460B. S/N: CATTH460CSLF01796. Hour meter reading: 2723 hrs. 3054E, 46 ft 3 section boom, hydraulic leveling.	
<a href="#">Click here for more information (308.8 KB)</a>		

Description source : <http://www.cat.com/cda/layout?m=111780&x=7>.

Capacity, reach, hp, and Hieght data:

[http://www.cat.com/cda/files/284659/7/Fabick\\_Cat\\_Equip.pdf](http://www.cat.com/cda/files/284659/7/Fabick_Cat_Equip.pdf).