Foamatic Cleaning System	
Mfg: Foamatic	Model: SCCS-1000
Stock No. CC-967.1	Serial No <u>.</u>

Foamatic Cleaning System. Model: SCCS-1000. Stainless steel construction. Foam/Rinse/Sanitize cycles. Temperature rated to 200 °F. Includes (5) discharge ports: (2) Foam, (2) Rinse, (1) Sanitize. Cat Pump, Model: 1010, capacity: 12 gpm, pressure range: 100 to 700 psi. Leroy Somer Motor, 5 hp, 1725 rpm, 230/460 V, 4.1/7.2 amps, 60 Hz, 3 phase. Inlets: (2) 3/4 in. dia. NPT (male). Outlets: (4) 3/4 in. dia. FNPT. Overall dimensions: 45 in. L x 23 in. W x 44 in. H.





















