

Moyno Pump Type SSQ

Mfg: Moyno

Model: Moyno Progressing Cavity Pump

Stock No. CCFP090.

Serial No.

Moyno Progressing Cavity Pump. Model: 1L10H. Type: SSQ. Capacity: 80-90 gpm @ 40 psi. Reliance Electric, 5 hp, 1165 rpm, 220-440 V, 15/7.5 amps, 60 Hz. 3.45: 1 pulley ratio. Final rpm: 337. Inlets/outlets: 3 in. Overall dimensions: 42 in. L x 66 in. W x 26 in. H.

