

## APV Crepaco Positive Pump

Mfg: APV Crepaco

Model: R6BSWF

Stock No. CCFP179.

Serial No. P-3880-96

APV Crepaco Positive Pump. Model: R6BSWF. S/N: P-3880-96. Sanitary, stainless steel. Pump displacement per revolution: 0.29 gallons. Maximum capacity: 150 gpm. Maximum rpm: 900. Flushed, double mechanical seal. Baldor motor, 7-1/2 hp, 1725 rpm, 208-230/460 V, 21.5-20/10 amps, 60 Hz, 3 phase. APG motor drive, 6.2 of ratio, final rpm: 278. Complete parts interchangeability. Easy disassembly and cleanup, low maintenance. Typical applications: fruit cocktail, yogurt, alcoholic beverages, doughs, chocolate and shampoo. Stainless steel base. Inlet/outlet: (2) 2-1/2 in. dia. S-line. Overall dimensions: 48 in. L x 15 in. W x 22 in. H.



