

## Gardner Denver Air Compressor

Mfg: Gardner Denver

Model: ADO

Stock No. CCFP396.

Serial No. 207982

Gardner Denver Air Compressor. Model ADO. S/N: 207982. Pressure: 125 lb ft, Class: GIA. Control Voltage: 208, 15 hp Wagner motor, 1,750 rpm, 208 V, 41 amps, 60 Hz, 2:1 pulley ratio, Pressed steel tank: 24 in. dia., Nat. Board #: 917777, Max WP 200 lbs. @ 650 °F, Overall dimensions: 71 in. L x 28 in. W x 72 in. H.

