

**1990 Hinds Bock Corp. Stainless Steel 4-Head Piston Filler- 1 Quart**

**Mfg: Hinds Bock**

**Model: 4P-128**

**Stock No. CESL011.**

**Serial No. 0001362**

1990 Hinds Bock Corp. Stainless Steel 4-Head Piston Filler- 1 Quart. Model: 4P-128. S/N: 0001362. Capacity: variable speeds up to 16 cycles per minute. Air requirements: 70-90 psi. Air use: 30 scfm @ 90 psig. Distance between heads: 3-1/8 in. Infeed hopper dimensions: 27 in. x L 32-1/2 in. W. System requirements: 208-220 V, 15 amps, 60/50 Hz, 3 phase. For high speed automatic container in feeding, indexing, bottom up filling, liquid depositing, and container discharging of thin liquids to heavy paste materials. Hoffman Electrical Interlock, Model: A-EK230NDH, 0.050/0.060 amps, 240/220 VAC, 60/50 Hz. GE Fanuc Series One PLC, Model: IC610PRG1058, 115 VAC input and 115 VAC output. Overall dimensions: 6ft. 3-1/2 in. L x 5ft. 8-1/4 in. W x 7ft. 5-3/4 in. H.





