

## Stainless Steel Volumetric Screw Feeder- 40 Gallon

**Mfg:**

**Model:**

**Stock No.: CFPH207**

**Serial No.:**

Stainless Steel Volumetric Screw Feeder- 40 Gallon. Inside straight-wall dimensions: 1 ft. 7-1/2 in. dia. x 2 ft. 6 in. L. Screw auger dimensions: 2-1/2 in. dia. x 1 ft. 2 in. L. Pitch: 2 in. Sew-Eurodrive Motor, 1/2 hp, 1700 rpm, 230/460 V, 2/1 amps, 60 Hz, 3 phase. Sew-Eurodrive Speed Reducer, ratio: 13.28, final speed: 128 rpm. Efficiently and accurately meters an infinite variety of dry materials: chemicals, foods, plastics, pharmaceuticals, metal powders. Inlets: (1) 19-1/2 in. dia. infeed, (1) 6 in. dia. port. Outlets: (1) 2-1/2 in. dia. port. Overall dimensions: 4 ft. 6 in. L x 1 ft. 11 in. W x 4 ft. 7 in. H.









DP133077108-25 TYPE 301  
 350223994.004 LWA.001  
 2307778607  
 2.00/1.00  
 3700  
 40

SEVERE DUTY MOTOR

350208443.004 LWA.004  
 117-2075  
 13.28  
 111  
 60B116EAR 630  
 100 60