

## Frick Vertical Ammonia Receiver- 130 Gallons

Mfg: Frick

Model:

Stock No. CFPH696.2a

Serial No. 75003

Frick Vertical Ammonia Receiver- 130 Gallons. S/N: 75003. Inside straight-wall dimensions: 4 ft. dia. x 10 ft. 4 in. H. Shell MAWP: 250 psig @ 100°F. MDMT: -20°F @ 250 psig. Inlets: (1) 4 in. dia. infeed port, (1) 1-1/2 in. dia. FNPT equalizer port. Outlets: (2) 1/2 in. dia. relief ports, (1) 1 in. dia. discharge port, (1) 3/4 in. FNPT drain port. Overall dimensions: 7 ft. 6 in. L x 6 ft. W x 13 ft. H.





NAT'L. BOARD SERIAL NO. 75003  
CERTIFIED BY **FPICK** COMPANY WAYNESBORO PENNA.

**SHELL CHAMBER**

U  
MAX. ALLOW. WORK. PRESS. 250 PSIG  
AT - 20 TO + 200 °F  
MIN. ALLOW. WORK. TEMP. °F  
MAWP AT MIN. TEMP. PSIG

**TUBE, COIL OR INNER CHAMBER**

MAX. ALLOW. WORK. PRESS. PSIG  
AT - + °F  
MIN. ALLOW. WORK. TEMP. °F  
MAWP AT MIN. TEMP. PSIG

MANUFACTURERS SERIAL NUMBER  
1227  
YEAR BUILT CRN NO.