

Foxboro Electronic Differential Pressure Transmitters

Mfg: Foxboro

Model: 843DP-H2I1SS

Stock No. CG-MM484.0

Serial No. 93452380

(4) Foxboro Electronic Differential Pressure Transmitters. Model: 843DP-H2I1SS. S/N's: 93452380, 93452381, 93452383, and 93452384. Maximum working pressure: 3000 psi. Cal: 4MA=0 (H2O). RNG: 20MA=207 (H2O). St: D. AS: E. Supply voltage: 12.5-36 VDC. Nema 4X enclosure. Inlets: (1) 3 in. dia. S-line fitting. Overall dimensions: 8 in. L x 5 in. W x 6-1/2 in. H.



