

## 2006 Weben-Jarco Direct Vented Water Boiler-19 HP

Mfg: Weben-Jarco

Model: EH075NG

Stock No.: CHMB004

Serial No.:

2006 Weben-Jarco Direct Vented Water Boiler-19 HP. Model: EH075NG. Nat'l Bd: 72026. Input capacity: 750,000 Btuh. Output capacity: 637,500 Btuh. Heating surface area: 112.5 sq. ft. MAWP: 160 psi @ 250°F. Minimum valve capacity: 1,125 lbs/hr. Minimum gas pressure: 4.0 in. W.C. Manifold pressure: 1.6 in. W.C. Cincinnati Fan & Ventilator Co. Blower, Model: PB-9, S/N: 515248-04. Baldor motor, 3/4 hp, 3450 rpm, 115/230 V, 11/5.5 amps, 60 Hz, single phase. Tank- 45 Gallon, inside straight-wall dimensions: 2 ft. dia. x 2 ft. H. Inlets: (1) 1-1/2 in. dia. water infeed port, (1) 6 in. dia. air intake port. Outlets: (1) 3/4 in. dia. port (regulator), (1) 1-1/2 in. dia. water discharge port, (1) 1-1/2 in. dia. port, (1) 6 in. dia. vent port. Weight: 650 lbs. Overall dimensions: 4 ft. 4 in. L x 2 ft. 7-1/4 in. W x 6 ft. H. (ACN119a).







