

Stainless Steel Pressure Wall Processor- 500 Gallon

Mfg:

Model:

Stock No. CJR12.5

Serial No.

Stainless Steel Pressure Wall Processor- 500 Gallon. Flip-top lids. Center bridge for agitation. Baffled. Inlets: (1) 3/4 in. dia. FNPT (thermowell), (1) 1 in. dia. port, (1) 1-1/2 in. dia. port to manifold, (1) 2 in. dia. MPT (jacket), (2) 2 in. dia. ports. Outlets: (1) 2-1/2 in. dia. MPT (jacket), (1) 3 in. dia. discharge. Overall dimensions 70 in. dia x 64 in. H.



