

## CPM Roskamp Champion Roller Mill

**Mfg: CPM Roskamp**

**Model: FRC90012**

**Stock No: CMSV002.**

**Serial No: R0S432299**

CPM Roskamp Champion Roller Mill. Model: FRC90012. S/N: R0S432299. Roller dimensions: 9 in. dia. x 12 in. L. Reliance Electric Motor, 7-1/2 Hp, 1755 rpm, 230/460 V, 21/10.5 amps, 60 Hz, 3 phase. Usable on 208 V, 26.7 amps. (2) Boston Gear Drives Ratio: 60:1, used to manually adjust roller gap. CPM Roller mills are meticulously engineered and highly efficient. They are built for continuous production. (4) 9 in dia. x 12 in. L form pressing wheels. Inlet: 5-1/4 in. port. Outlet: (1) 4 in. dia. port, (1) 13 in. W x 8-1/2 in. L flange port. Overall dimensions: 4 ft. 7-3/4 in. L x 2 ft. 10 in. W x 5 ft. 5 in. H. (ACN550).







