

## Unused Waukesha 15 Positive Displacement Pump with Jacketed Faceplate

**Mfg: Waukesha**

**Model: 15**

**Stock No: CNAT02.10**

**Serial No: 14992 SS**

Unused Waukesha 15 Positive Displacement Pump with Jacketed Faceplate. Model: 15. S/N:14992 SS. Flow rate for new pump is 9 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Steam jacket cover. Graham cone drive with Shimpo controller. Pump, motor and drive are mounted on a stainless steel plate. Graham ring cone drive, required input rpm: 1750, output rpm: 0.9 to 90.9, output torque: 2170 LB-IN at high speed, 513 LB-IN at low speed. Graham gear reducer ratio: 11:1. Inlets/outlets: (2) 1 in. I-Line fittings. Overall dimensions for control box: 1 ft. 4 in. L x 10-1/2 in W x 1 ft. 10-1/2 in. H. Overall dimensions for pump: 3 ft. 8-1/2 in. x 10 in. W x 1 ft. 8-1/2 in H.(ACN128).













