

Waukesha 30 Positive Displacement Pump

Mfg: Waukesha

Model: 030

Stock No: DBBP185418.13

Serial No: 291801 R2 01

Waukesha Positive Displacement Pump. Model: 30. Serial No: 291801 R2 01. Flow rate for new pump is 36 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. (2) 4-1/8 in. rotors. TB Woods Variable Frequency drive: E-Trac WFC4002-OCHT, serial no. 99290283. Input 380-460 volts, 50/60 Hz, 4.3 amps, and 3 phase. Output 2 hp, 460 volts, 4.1 amps, and 3 phase. Reliance Electric drive: 5.0 ratio, 1750 input rpm, and 281 torque. Reliance Electric motor: 2 hp, 1725 rpm, 208-230/460 volts, 6.4-6.4/3.2 amps, 60 Hz, 3 phase. (1) 1-1/2 in. s-line inlet. (1) 1-1/2 in. s-line outlet. Overall dimensions: 3 ft. 3 in. L. x 1 ft. 3-1/8 in. W. x 3 ft. 8 in. H.(ACN71).









